

## Product data sheet

### Characteristics

# SAU3DC12182DF

SAU Chassis, Acti9, 250A, 2Ph, 12 poles,  
18mm for iC60 MCB and RCBO, dual feed

### Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

### Complementary

Range compatibility	Acti 9 distribution board
Network type	AC/DC
[In] rated current	250 A
Number of ways	1 way (incomer) - 2P
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	12
Number of poles	12 x 18 mm
Width	215 mm
Length	110 mm
Busbar pitch	18 mm
Location of connection	Dual feed

### Environment

Standards	AS/NZS 61439
-----------	--------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.5 cm
Package 1 Length	39.4 cm
Package 1 Weight	1.5 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.