

## Product data sheet

### Characteristics

# SAUPW163

Moulded Switchboard Enclosure, MAX9, 63A, 1P, 10kA MCB, Surface Mount, Shallow Base

### Main

Range	MAX9
Product or component type	Enclosure
Product brand	Clipsal
Poles description	1P
Curve code	C
Device application	Distribution

### Complementary

Provided equipment	Enclosure Miniature circuit breaker (MCB) (1) 1P 63 A 240 V AC Sealing kit Pole filler Padlocking kit
[In] rated current	63 A
[Ue] rated operational voltage	240 V AC 50/60 Hz
Breaking capacity	10 kA at 240 V AC 50/60 Hz
Enclosure material	thermoplastic
Device mounting	Surface
Mounting support	DIN rail
Width	53 mm
Height	133 mm
Depth	95 mm
Total number of 18 mm modules	2
Provision for padlocking	Padlockable
Cable entry	Top and bottom Rear entry

### Environment

IP degree of protection	IP30
Ambient air temperature for operation	-25...70 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.2 cm
Package 1 Width	16.4 cm
Package 1 Length	24.8 cm
Package 1 Weight	402.0 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>