

Product data sheet

Characteristics

SEA9BN12TNA

Acti9, Isobar B - panel fixing pan assembly - 12 ways TP&N



Main

Range	Acti9
Product or component type	Pan assembly
Device application	Distribution

Complementary

Range compatibility	Acti9 (Acti9 Isobar B) distribution board
Provided equipment	Mounting plate
[In] rated current	250 A
Rated voltage	415 V AC 50/60 Hz
Short-circuit withstand	25 kA 0.1 s
[Icw] rated short-time withstand current	25 kA
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Incomer device options	3P switch disconnecter 3P terminal block 3P MCCB
Protection device options at outgoer	Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Miniature circuit breaker (MCB) 63 A max
Number of ways	1 way (incomer) - 3P + N 12 ways (outgoer)
Outgoer Pole capacity	36 x 18 mm
Busbar pitch	18 mm
Length	398 mm
Width	210 mm
Depth	90 mm

Environment

Standards	IEC 61439
-----------	-----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	22.0 cm
Package 1 Length	40.0 cm
Package 1 Weight	5.722 kg
Unit Type of Package 2	PAM

Number of Units in Package 2	96
Package 2 Height	112.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	569.312 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product