



Main

Product brand	Clipsal
---------------	---------

Complementary

Curve code	C
Number of poles	2
[In] rated current	40 A
Number of modules	2
[Ue] rated operational voltage	500 V
Breaking capacity	6 kA conforming to IEC 60947-2
Network type	DC
[Uimp] rated impulse withstand voltage	6 kV
[Ui] rated insulation voltage	500 V
Mechanical durability	20000 cycles
Connections - terminals	Screw terminal for 1 cable(s) 1...35 mm ² rigid Screw terminal for 1 cable(s) 1...25 mm ² flexible Screw terminal for 1 cable(s) 1...25 mm ² flexible with ferrule
Wire stripping length	14 mm
Tightening torque	3.5 N.m

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Standards	AS/NZS 60898
Pollution degree	3
Relative humidity	95 % at 55 °C
Height	81 mm
Width	36 mm
Depth	78.5 mm
Net weight	256 g

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	8.5 cm
Package 1 Length	3.6 cm
Package 1 Weight	243.4 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations