

## Product data sheet

### Characteristics

# SRVS3KI-AZ

## Easy UPS On-Line SRVS 3000VA 230V, Australia



### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Rated power in W	2400 W
Rated power in VA	3000 VA
Output voltage	230 V
Output voltage	220 V 240 V
Plug standard	IEC 60320 C14
Cable length	1.48 m
Number of cables	1

### General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Provided equipment	Basic UPS signalling RS-232 cable CD with software User manual USB cable

### Physical

Mounting mode	Not rack-mountable
Height	33.6 cm
Width	19 cm
Depth	42.5 cm
Product weight	26.8 kg
Colour	Black

### Input

Input voltage	230 V
Input voltage	220 V 240 V
Input voltage limits	110...285 V half load 160...280 V full load
Network frequency	40...70 Hz auto sensing

## Output

Maximum configurable power in VA	3000 VA
Maximum configurable power in W	2400 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
UPS type	Double conversion online
Wave type	Sine wave
Efficiency	88 % (full load)
Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1

## Conformance

Product certifications	CE
Standards	EN/IEC 62040-1 EN/IEC 62040-2

## Environmental

Acoustic level	50 dBA
Operating altitude	0...3000 m
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-20...50 °C
Storage altitude	0...15000 m
IP degree of protection	IP20
Relative humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % Non-condensing

## Batteries & Runtime

Battery type	Lead-acid battery
Battery voltage	72 V
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	4 h
Battery life	3...5 year(s)
Battery charger power	118 W rated

## Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm
Control panel	Multifunction LCD status and control console
Free slots	1

## Surge Protection and Filtering

Surge energy rate	600 J
-------------------	-------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	29 kg
Package 1 Height	46.5 cm
Package 1 width	32.5 cm
Package 1 Length	56.5 cm

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------