



## Main

|                           |                                     |
|---------------------------|-------------------------------------|
| Range of product          | Series 56                           |
| Range                     | Clipsal - 56 Series                 |
| Product brand             | Clipsal                             |
| Product or component type | Switch                              |
| Device presentation       | Basic element with full cover plate |
| Device application        | Control                             |
| Colour                    | Cover: grey                         |
| Handle colour             | Grey                                |
| Suitability for isolation | Yes                                 |

## Complementary

|   |                    |
|---|--------------------|
| Switch function                           | 3-pole             |
| Poles description                         | 3P                 |
| [Icm] rated short-circuit making capacity | 2.1 kA             |
| Control type                              | Rotary knob        |
| Number of poles                           | 3                  |
| Device mounting                           | Surface            |
| Fixing mode                               | By screws          |
| Material                                  | PC (polycarbonate) |
| Tightening torque                         | 0.8 N.m            |
| Local signalling                          | without            |
| [Ue] rated operational voltage            | 500 V AC 50 Hz     |
| Rated current                             | 20 A               |
| Marking                                   | ON-OFF             |
| Marking location                          | Marking on surface |
| Height                                    | 107 mm             |
| Width                                     | 101 mm             |
| Depth                                     | 108 mm             |
| Net weight                                | 0.7 kg             |
| Breaking capacity                         | 20 kA              |
| Targeted country                          | Australia          |
| Rotary handle padlocking                  | 2 padlocks 8 mm    |
| [Icw] rated short-time withstand current  | 1.5 kA for 1 s     |
| [Uimp] rated impulse withstand voltage    | 4 kV               |
| Motor M-rating AS3133                     | M150 at 500 V      |

## Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Ambient air temperature for operation | -25...75 °C                 |
| IP degree of protection               | IP66 conforming to AS 60529 |
| Standards                             | AS/NZS 3133                 |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 11.0 cm |
| Package 1 Width              | 10.6 cm |
| Package 1 Length             | 11.0 cm |
| Package 1 Weight             | 691.0 g |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           |  <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant with Exemptions   |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information |  <a href="#">Yes</a>                           |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations  |