

Product data sheet

Characteristics

SSM2A16BD

Solid state modular relay, Harmony Solid State Relays, 6A, DIN rail mount, zero voltage switching, input 4...32V DC, output 24...280V AC



Main

Range of product	Harmony Solid State Relays
Product or component type	Modular DIN rail relay
Device short name	SSM
Number of channels	2
Number of phases	1 phase
Output switching mode	Zero voltage switching

Complementary

Mounting support	Symmetrical DIN rail
[In] rated current	6 A
Output voltage	24...280 V AC
[Uc] control circuit voltage	4...32 V DC
Tightening torque	0.5...0.8 N.m for input 0.5...0.8 N.m for output
Connections - terminals	Screw terminals: 1 x 0.3...1 x 1.5 mm ² , (AWG 22...AWG 16) for input Screw terminals: 1 x 0.3...1 x 2.5 mm ² , (AWG 22...AWG 14) for output
Maximum capacitance	10 pF for input/output
Insulation resistance	1000 MOhm at 500 V DC
Local signalling	LED (green) for input status
Minimum switching voltage	4 V DC turn-on
Maximum switching voltage	1 V DC turn-off
Input current	14...16.87 mA
Solid state output type	SCR output Zero voltage switching
Load current	0.15...6 A
Transient overvoltage	600 V
Surge current	715 A for 16.6 ms 750 A for 20 ms
Maximum voltage drop	<1.3 V on-state
Motor power hp	0.16 hp 40 °C 240 V AC
Maximum I ² t for fusing	2560 A ² .S for 10 ms at 50 Hz 2330 A ² .s for 8.33 ms at 60 Hz
Maximum leakage current	0.1 mA off-state
DV/dt	500 V/μs off-state at maximum voltage
Response time	0.5 cycle (turn-on) 0.5 cycle (turn-off)
Power factor	0.5 (with maximum load)
Overvoltage category	III
Width	18 mm

Height	90.3 mm
Test button	Without test button
Depth	84.4 mm
Net weight	0.09 kg

Environment

Flame retardance	V0 conforming to UL 94
Dielectric strength	2.5 kV AC for input/output 2.5 kV AC for input or output to case
Pollution degree	2
Standards	IEC 61000 IEC 60950-1 IEC 62314
Product certifications	CSA[RETURN]UL
Marking	CE
IP degree of protection	IP20
Ambient air temperature for operation	-30...80 °C
Ambient air temperature for storage	-30...100 °C


Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	9.0 cm
Package 1 Length	9.0 cm
Package 1 Weight	98.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	72
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.458 kg


Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Dimensions



Derating Curves



A : Load Current (Amperes)

B : Ambient Temperature (°C)

1 : Multiple units, no minimum spacing between components

2 : Installed single unit, distance to adjacent components more than 18 mm