



Main

| | |
|-------------------------|----------------------|
| Product brand | Clipsal |
| Range of product | Series 7 |
| Electrical circuit type | Changeover contactor |

Complementary

| | |
|---|----------------------|
| Switch function | 2-way |
| Mounting holes diameter | 9 mm |
| [Us] rated supply voltage | 415 V DC |
| Number of contacts | 2 |
| Connector type | Screw terminals |
| [Ui] rated insulation voltage | 480 V AC |
| [Ith] conventional free air thermal current | 10 A |
| Number of poles | 3 |
| Rated operational power in W | 3 kW |
| Switching angle | 60 ° |
| Fuse type | 3 KA, gG 3 kA, gL |
| Maximum short-circuit current | 10 A |

Environment

| | |
|-------------------------|------|
| IP degree of protection | IP20 |
|-------------------------|------|

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 0.8 cm |
| Package 1 Width | 0.8 cm |
| Package 1 Length | 4.5 cm |
| Package 1 Weight | 3 g |

Offer Sustainability

| | |
|---------------------|--|
| EU RoHS Directive | Under investigation |
| Circularity Profile | No need of specific recycling operations |