



Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Vertical
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	105 mm
Width	55 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	5.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	0.168 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	117 cm

Package 2 Width	143 cm
Package 2 Length	181 cm
Package 2 Weight	1.68 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	254 cm
Package 3 Width	348 cm
Package 3 Length	445 cm
Package 3 Weight	16.8 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	End Of Life Information