

## Product data sheet

### Characteristics

# VW3A9920

## Altivar 32, Mechanical adaptor for 90° control mounting



### Main

Range of product	Altivar
Product or component type	Adaptor plate
Accessory / separate part category	Mounting and fixing accessory
Product compatibility	Variable speed drive ATV320...B, 0.18...2.2 kW, 200...240 V, single phase Variable speed drive ATV320...B, 0.37...4 kW, 380...500 V, three phase Variable speed drive ATV32, 0.18...2.2 kW, 200...240 V, single phase Variable speed drive ATV32, 0.37...4 kW, 380...500 V, three phase
Accessory / separate part destination	Control block

### Complementary

Sale per indivisible quantity	1
Net weight	0.125 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	17.000 cm
Package 1 Length	23.000 cm
Package 1 Weight	256.000 g
Unit Type of Package 2	P06
Number of Units in Package 2	56
Package 2 Height	73.500 cm
Package 2 Width	80.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	27.336 kg

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

### Contractual warranty

Warranty	18 months
----------	-----------