

Product data sheet

Characteristics

XARSK8D18H

Harmony eXLhoist, System with charger, standard, shoulder belt, cable USB/RJ45 and config software, for control station



Main

Range of product	Harmony eXLhoist
Product or component type	Control station
Device short name	XARS
Control station type	Wireless
Product specific application	Material handling Hoisting applications
Number of channels	50
Control station application	Stop function: SIL 2 maximum (can reach PL d/ category 3) conforming to EN/IEC 62061 Stop function: SIL 2 maximum (can reach PL d/ category 3) conforming to EN/ISO 13849-1 Emergency stop function: SIL 3 maximum (can reach PL e/category 4) conforming to EN/IEC 62061 Emergency stop function: SIL 3 maximum (can reach PL e/category 4) conforming to EN/ISO 13849-1 Motion function: SIL 1 maximum (can reach PL c/ category 1) conforming to EN/IEC 62061 Motion function: SIL 1 maximum (can reach PL c/ category 1) conforming to EN/ISO 13849-1 Limiter protection function: SIL 1 maximum (can reach PL c/category 1) conforming to EN/IEC 62061 Limiter protection function: SIL 1 maximum (can reach PL c/category 1) conforming to EN/ISO 13849-1

Complementary

Kit composition	Base station Cable Shoulder belt Configuration software Remote control
Operating distance	100 m in free air
Connector type	Industrial socket
Cable entry	Cable gland
Communication network type	Wireless: bluetooth low energy
Transmission frequency	2.4 GHz

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Radio agreement	ARIB RSS FCC ANATEL SRRC ICASA
Relative humidity	0...95 % at -20...45 °C storage
Electromagnetic compatibility	Resistance to electrostatic discharge - test level: 4 kV class B (on contact) conforming to IEC 61000-4-2 Resistance to electrostatic discharge - test level: 8 kV class B (in air) conforming to IEC 61000-4-2 Resistance to radiated electromagnetic fields - test level: 10 V/m class B conforming to IEC 61000-4-3
Standards	EN/IEC 60204-1 safety EN/ISO 13849-1 safety EN/IEC 62061 safety EN/IEC 61508 safety EN/ISO 13850 safety EN/IEC 60204-32 hoisting applications EN 13557 hoisting applications EN 12077-2 hoisting applications EN 15011 hoisting applications EN 14439 hoisting applications EN 14492 hoisting applications ETSI EN 301 489-1 radio ETSI EN 301 489-3 radio ETSI EN 301 489-17 radio ARIB STD-T81 radio
Product certifications	CE[RETURN]UL[RETURN]CSA[RETURN]C-Tick[RETURN]JIS[RETURN]KC[RETURN]EAC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.0 cm
Package 1 Width	28.5 cm
Package 1 Length	30.5 cm
Package 1 Weight	3.089 kg
Unit Type of Package 2	S04
Number of Units in Package 2	2
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	7.131 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins