

B15VM-WE

Metal Plate Series, Single Switch Socket Outlet Mechanism, 250V, 10A, B Style, Flat Plate, Vertical

Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal

Complementary


Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number Of Outlets	1
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Vertical
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	32.5 mm
Length	95 mm
Width	55 mm
Mounting Centers	84 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	5.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	68 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	11.7 cm
Package 2 Width	14.3 cm
Package 2 Length	18.1 cm
Package 2 Weight	680 g
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	25.4 cm

Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	6800 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations