



Main

Range	Clipsal
Product name	TPHB Series
Product or component type	High bay light
Device application	Lighting
Type of installation	Indoor/outdoor
Market segment	Industrial buildings Commercial

Complementary

Environmental characteristic	Harsh environment
Light source	LED 150 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =80
Luminous flux	18500 lm
Colour temperature	5000 K
Beam angle	120 °
Mounting mode	By hook
Provided equipment	Flex Plug
IP degree of protection	IP65
Electrical insulation class	Class I
Material	Die cast aluminium housing Acrylic lens
Width	360 mm
Diameter	360 mm
Net weight	4.0 kg




Environment

Total system power	150 W
Bulb lifespan	50000 h
Ambient air temperature for operation	-10...50 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	22 cm
Package 1 Width	41.5 cm
Package 1 Length	41.5 cm
Package 1 Weight	5.26 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes