



Main

Range of product	Thorsman
Product or component type	Double cable wing
Provided equipment	With nail plug
Device application	Cable installation two sides Conduit installation two sides
Colour tint	Dark grey
Quantity per set	Set of 25

Complementary

Type of installation	Indoor/outdoor
Number of cables	6 x 0...12 mm: both side
Practical load capacity	30 N
Material	Cable wing: PA (polyamide) Nail plug: PA (polyamide) Nail: steel electroplated
Height	23 mm
Width	20 mm
Depth	230 mm

Environment



Ambient air temperature for operation	-20...60 °C
Environmental characteristic	Withstand extreme temperature High UV resistance

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	2.3 cm
Package 1 Length	23.0 cm
Package 1 Weight	25.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Contractual warranty	
Warranty	18 months