



### Main

Cabling installation system	Pole Post
Product or component type	Floor feeder

### Complementary

Type of pole	One-sided Two installation boxes Two-sided One installation box
Type of post	One-sided Two-sided
Colour tint	Grey (RAL 7030)
Quantity per set	28 m
Pole/post surface finish	Anodized Powder coated
Pole fixing mode	Tension-mounted
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	18 mm
Width	75 mm
Market segment	Small commercial Residential

### Environment

Standards	EN 50085-1:2005 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	2
Package 1 Height	2.0 cm
Package 1 Width	8.5 cm
Package 1 Length	200.0 cm
Package 1 Weight	1.06 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	28
Package 2 Height	9.0 cm
Package 2 Width	21.0 cm

Package 2 Length	202.0 cm
Package 2 Weight	15.0 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	448
Package 3 Height	65.0 cm
Package 3 Width	120.0 cm
Package 3 Length	210.0 cm
Package 3 Weight	261.0 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#"> EU RoHS Declaration</a>
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------