

KDP20ABG4

Canalis, End feed unit, Canalis KDP20, 20A, right or left mounting, without line protection, 3L +N+PE



Main

Range of product	Canalis
Device short name	KDP
Product compatibility	Canalis KDP busbar trunking 20 A
Product or component type	Feed unit
Conductors material	Copper
[Ie] rated operational current	20 A
[Ue] rated operational voltage	230...400 V
Number of circuits	1
Busbar trunking polarity	3L + N + PE
Protection type	Without protection
Control type	Without

Complementary

Provided equipment	End cover
Mounting location	Left Right
Mounting mode	By clips
Mounting support	Busbar
Connections - terminals	Terminal block - Pg 16 - screw clamp connector for 4 mm ²
Width	159 mm
Depth	64 mm
Height	49 mm
Net weight	120 g
Standards	IEC 61439-6

Environment

IP degree of protection	IP55 conforming to IEC 60529
-------------------------	------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.0 cm
Package 1 Width	13.0 cm
Package 1 Length	6.0 cm
Package 1 Weight	192.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	25
Package 2 Height	20.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.8 kg
Unit Type of Package 3	P06

Number of Units in Package 3	300
Package 3 Height	77.0 cm
Package 3 Width	80.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	90.1 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------