

LC2D09KUE

TeSys; TeSys Deca, Reversing contactor, 3P(3 NO), AC-3, 0 to 440V, 9A, 100 to 250VAC/DC coil





Associated fuse rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 25 A gG at ≤ 690 V coordination type 1 for power circuit 20 A gG at ≤ 690 V coordination type 2 for power circuit
Average impedance	2.5 mOhm - Ith 25 A 50 Hz for power circuit
[Ui] rated insulation voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-1
Electrical durability	2.4 Mcycles 8 A AC-3 at Ue ≤ 440 V 0.6 Mcycles 25 A AC-1 at Ue ≤ 440 V 2.4 Mcycles 8 A AC-3e at Ue ≤ 440 V
Power dissipation per pole	1.56 W AC-1 0.2 W AC-3 0.2 W AC-3e
Front cover	With
Interlocking type	Mechanical
Mounting support	Plate Rail
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 IEC 60335-1
Product certifications	CCC[RETURN]CSA[RETURN]EAC[RETURN]UL[RETURN]KC[RE GL[RETURN]LROS (Lloyds register of shipping) [RETURN]UKCA
Connections - terminals	Power circuit: screw clamp terminals 1 cable(s) 1... 4 mm²flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 1... 4 mm²flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 1... 4 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1... 2.5 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 1... 4 mm²solid Power circuit: screw clamp terminals 2 cable(s) 1... 4 mm²solid Control circuit: screw clamp terminals 1 cable(s) 1... 4 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1... 4 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 1... 4 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1... 2.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1... 4 mm²solid Control circuit: screw clamp terminals 2 cable(s) 1... 4 mm²solid
Tightening torque	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Operating time	45...55 ms closing 20...90 ms opening
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical durability	15 Mcycles
Maximum operating rate	3600 cyc/h 60 °C

Complementary

Coil technology	Built-in bidirectional peak limiting
Control circuit voltage limits	$\leq 0.1 U_c$ (-40...70 °C):drop-out AC/DC 0.85...1.1 U_c (-40...60 °C):operational AC/DC 1...1.1 U_c (60...70 °C):operational AC/DC
Inrush power in VA	25 VA 50/60 Hz (at 20 °C)
Inrush power in W	18 W at 20 °C
Hold-in power consumption in VA	1.6 VA (at 20 °C) 50/60 Hz
Hold-in power consumption in W	1.1 W at 20 °C
Heat dissipation	1.1 W at 50/60 Hz
Auxiliary contacts type	Type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 Type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling circuit frequency	25...400 Hz
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Non-overlap time	1.5 Ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Insulation resistance	> 10 MOhm for signalling circuit

Environment

IP degree of protection	IP20 front face conforming to IEC 60529
Climatic withstand	Conforming to IACS E10 Conforming to IEC 60947-1 Annex Q category D
Protective treatment	TH conforming to IEC 60068-2-30
Pollution degree	3
Ambient air temperature for operation	-40...60 °C 60...70 °C with derating
Ambient air temperature for storage	-60...80 °C
Operating altitude	0...3000 m
Fire resistance	850 °C conforming to IEC 60695-2-1
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Vibrations contactor open: 2 Gn, 5...300 Hz Vibrations contactor closed: 4 Gn, 5...300 Hz Shocks contactor open: 10 Gn for 11 ms Shocks contactor closed: 15 Gn for 11 ms
Height	77 mm
Width	90 mm
Depth	86 mm
Net weight	0.783 kg
Colour	Grey (SE GREY 6) Green (SE GREEN 2)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	11.4 cm
Package 1 Length	14.0 cm
Package 1 Weight	878.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	6
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.583 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts & cables product

Contractual warranty

Warranty	18 months
----------	-----------