



Main

Range	Clipsal Iconic
Product or component type	Switched socket
Device presentation	Complete product
Outlet poles configuration	2P + E with shutter
Outlet standard	Australian

Complementary

Device mounting	Flush
Number of power socket outlets	1
Number of rocker	1
Range compatibility	Clipsal Iconic
Outlet standard description	With earthing contact
Outlet standard	Australian/New Zealand
Ground lug position	Straight 180° position
Number of gangs	1 gang
Fixing mode	By screw
Installation direction	Horizontal
Surface finish	Matt
Type of packing	Polybag
Quantity per set	Set of 10
Sale per indivisible quantity	1
Rated current	10 A at 250 V AC 50 Hz
Electrical durability	12000 cycles
Connections - terminals	3 screw terminals
Screwdriver shape	Philips No 2 Square drive no 1 (SQ1)
Clamping connection capacity	1 x 2.5...4 x 2.5 mm ² for rigid cable(s) 1 x 2.5...4 x 2.5 mm ² for stranded cable(s) 1 x 2.5...4 x 2.5 mm ² for flexible cable(s)
Wire stripping length	16 mm
Material	PC (polycarbonate): fixing frame PP (polypropylene): rocker POM (polyoxymethylene): shutter PC (polycarbonate): cover frame ABS (acrylonitrile butadiene-styrene): cover frame POM (polyoxymethylene): locking bar
Height	78 mm
Width	120 mm
Depth	31 mm
Embedding depth	23 mm
Net weight	0.1 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.






Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZS 3112
Product certifications	RCM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	7.8 cm
Package 1 Length	12 cm
Package 1 Weight	84 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	11.2 cm
Package 2 Width	15 cm
Package 2 Length	32.8 cm
Package 2 Weight	1.402 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	33.5 cm
Package 3 Width	26.1 cm
Package 3 Length	33.5 cm
Package 3 Weight	5.388 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations