


40CSFM

Clipsal Iconic, Fan Speed Controller, 4-Position, Rotary Switch Off-1-2-3 Capacitor, 5 Colour Options



Main

Range	Clipsal Iconic
Product or component type	Selector switch
Device application	Fan speed controller
Colour tint	Vivid white
Quantity per set	Set of 10

Complementary

Device presentation	Mechanism
Control type	Rotary knob
Switch function	4 positions
Marking	0 - 1 - 2 - 3
[Ue] rated operational voltage	250 V
Material	Plastic
Connections - terminals	Screw terminal
Height	23 mm
Width	23 mm
Depth	51 mm
Net weight	0.042 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	7.3 cm
Package 1 Length	10.2 cm
Package 1 Weight	50 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	32.8 cm
Package 2 Width	10.6 cm
Package 2 Length	14.6 cm
Package 2 Weight	500 g
Unit Type of Package 3	CAR
Number of Units in Package 3	120
Package 3 Height	33.5 cm
Package 3 Width	26.1 cm
Package 3 Length	33.5 cm
Package 3 Weight	6000 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information