



Main

Range of product	900 Series
Product or component type	Plug
Material	PC (polycarbonate)
Colour tint	White

Complementary

Surface finish	Gloss
Width	45 mm
Diameter	45 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Pin number	3
Ambient air temperature for operation	-10...40 °C
Cable cross section	0.75...1.5 mm ²
Connector type	Screw terminals
Quantity per set	Set of 10
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	5.5 cm
Package 1 Length	6 cm
Package 1 Weight	0.049 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	140
Package 2 Height	25 cm
Package 2 Width	27.5 cm
Package 2 Length	39.7 cm
Package 2 Weight	8620.0 g
Unit Type of Package 3	PAL
Number of Units in Package 3	6720
Package 3 Height	140 cm
Package 3 Width	114 cm
Package 3 Length	114 cm
Package 3 Weight	329.28 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations