



Main

Product brand	Clipsal
---------------	---------

Complementary

Curve code	C
Number of poles	2
[In] rated current	100 A
Number of modules	3
[Ue] rated operational voltage	415 V
Breaking capacity	10 kA conforming to IEC 60947-2
Network type	AC
Network frequency	50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
[Ui] rated insulation voltage	500 V
Mechanical durability	20000 cycles
Electrical durability	5000 cycles
Connections - terminals	Screw terminal for 1 cable(s) 1...50 mm ² rigid Screw terminal for 1 cable(s) 1.5...35 mm ² flexible Screw terminal for 1 cable(s) 1.5...35 mm ² flexible with ferrule
Wire stripping length	15 mm
Tightening torque	3.5 N.m

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Standards	AS/NZS 60898
Pollution degree	3
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Height	91 mm
Width	54 mm
Depth	78.5 mm
Net weight	410 g

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	5.5 cm
Package 1 Length	9 cm
Package 1 Weight	386 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile