

## Product data sheet

### Characteristics

# 10MDSLБ-WE

## Standard Series, Automatic Single Switch Socket Outlet Mechanism, 250VAC, 10A



### Main

|                           |                  |
|---------------------------|------------------|
| Range of product          | Standard Series  |
| Product or component type | Socket-outlet    |
| Colour                    | White electric   |
| Product brand             | Clipsal          |
| Quantity per set          | Set of 1         |
| Cover type                | Complete housing |

### Complementary

|                                |                         |
|--------------------------------|-------------------------|
| Colour code                    | WE                      |
| Marking                        | Without marking         |
| Protection type                | Fingersafe              |
| Local signalling               | Without light indicator |
| Device mounting                | Flush                   |
| Fixing mode                    | By screws               |
| [In] rated current             | 10 A                    |
| [Ue] rated operational voltage | 250 V AC                |
| Depth                          | 33 mm                   |
| Length                         | 60 mm                   |
| Width                          | 42 mm                   |
| Fixing center                  | 50 mm                   |
| Number of poles                | 2                       |

### Environment

|           |   |
|-----------|---|
| Standards | AS/NZS 3100<br>AS/NZS 3112<br>AS/NZS 3133:approval number S/1 |
|-----------|---|

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type of Package 1       | PCE    |
| Number of Units in Package 1 | 1      |
| Package 1 Height             | 3.5 cm |
| Package 1 Width              | 4.2 cm |
| Package 1 Length             | 6 cm   |
| Package 1 Weight             | 50 g   |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                          |   |
|--------------------------|---|
| REACH Regulation         | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive        | Compliant with Exemptions                     |
| China RoHS Regulation    | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a> |
| Circularity Profile      | No need of specific recycling operations      |