

Product data sheet

Characteristics

230DRAQTTP

Resimax Meterbox 21 module - H680 x W470 x D280 mm Temporary supply



Main

Range of product	Resi MAX
Product type	Meter box
Enclosure type	Plain door enclosure
Device application	Metering Distribution
Targeted country	Queensland

Complementary

Enclosure mounting	Semi flush Surface
Number of modules	21
Provided equipment	Fascia plate Removable meter panel Earth and neutral grid assembly DIN rail Enclosure
Function available	Cable protection slide Clips lead retainer
Protection device type	Miniature circuit breaker (MCB) - 63 A - 2P - 6 kA
Cable entry	Knock-out top and bottom Knock-out rear
Type of door	Ventilated removable door with door retainer
Door opening side	Right
Lock type	Padlockable
Material	Iron (galvanised)
Surface finish	Epoxy powder coat
Width	470 mm
Height	680 mm
Depth	280 mm
Colour	Beige

Environment

IP degree of protection	IP23
Standards	AS/NZS 3000

Packing Units

Package 1 Weight	16.500 kg
Package 1 Height	700.000 mm
Package 1 width	295.000 mm
Package 1 Length	489.000 mm

