


# Product data sheet

## Characteristics

# 2D4P6IPV3B-BU

Clipsal Actassi, LAN Cable, 305m, Category 6, UTP



### Main

Range of product	Titanium
Product brand	Clipsal
Colour	External sheath: blue

### Complementary

Communication network category	6
AWG gauge	AWG 23
Cable shielding type	UTP
Cable insulation material	PVC (polyvinyl chloride)
Material	Conductor: bare copper
Diameter	0.546...0.556 mm (conductor)
External diameter	6.1 mm
Length	305 m
Colour code	BU

### Environment

Ambient air temperature for operation	75 °C
Flame retardance	CM
Standards	ANSI/TIA/EIA-568-B ISO/IEC 11801

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.0354 cm
Package 1 Width	0.0272 cm
Package 1 Length	0.0344 cm
Package 1 Weight	0.045 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations