

Product data sheet

Characteristics

438-WE

Standard Series, Flexible Cord Extension Socket, 250VAC, 10A, 3 Pin



Main

| | |
|---------------------------|------------------|
| Range of product | Standard Series |
| Product or component type | Socket-outlet |
| Colour | White electric |
| Product brand | Clipsal |
| Quantity per set | Set of 1 |
| Cover type | Complete housing |

Complementary

| | |
|--------------------------------|--------------------------|
| Colour code | WE |
| Marking | Without marking |
| Local signalling | Without light indicator |
| Material | PVC (polyvinyl chloride) |
| [In] rated current | 10 A |
| [Ue] rated operational voltage | 250 V AC |
| Depth | 71 mm |
| Diameter | 43 mm |




Environment

| | |
|-----------|--|
| Standards | AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1 |
|-----------|--|

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9 cm |
| Package 1 Width | 10 cm |
| Package 1 Length | 4.5 cm |
| Package 1 Weight | 58 g |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |

