

Product data sheet

Characteristics

4RCBE232/10

Residual current breaker with overcurrent protection (RCBO), MAX4, 2P, 32 A, C curve, 6000 A, 240 V, 10 mA, A type



Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Poles description	2P
Number of modules	2
[In] rated current	32 A
Curve code	C
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Type A
Breaking capacity	6000 A

Complementary

[Ue] rated operational voltage	240 V AC
[Uimp] rated impulse withstand voltage	4 kV
Size	81 x 36 x 77.5 mm conforming to DIN 43880

Environment

Standards	AS/NZS 61009
IP degree of protection	IP20 IP40
Ambient air temperature for operation	-5...40 °C

Packing Units

Package 1 Weight	211.000 g
Package 1 Height	86.000 mm
Package 1 width	102.000 mm
Package 1 Length	41.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.