



Main

Range	Infrascan
Product brand	Clipsal
Product or component type	Movement sensor
Colour	White electric

Complementary

[Ue] rated operational voltage	200...265 V
Mounting support	Ceiling Wall
Mounting height	2.4 m
Colour code	WE

Environment

Ambient air temperature for operation	0...40 °C
---------------------------------------	-----------

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Circularity Profile	End Of Life Information

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.