

# Product data sheet

## Characteristics

# 753CF2

Motion Sensor Infrascan - Passive infrared -  
Indoor - Two-channel - 3.5m detection radius -  
240 V



### Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	LED lighting: : 100 W Compact fluorescent lamp: : 100 W Motor: : 100 W Relay: : 5 A - 250 V Incandescent lamps: : 1000 W - 230 V Halogen lamp: : 900 W - 230 V Halogen lamp with standard electronic transformer: 250 VA Halogen lamp with standard ferromagnetic transformer: 500 VA Capacitive: : 6 A, 21 µF Capacitive: : 10 A, 14 µF Fluorescent tube: 200 VA
Colour tint	White

### Complementary

Network frequency	50/60 Hz
Input function	Switch
Output voltage	220...250 V
Output current	10 A
Number of channels	2
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	5...1000 lux
Horizontal detection angle	360 °
Cable length	0.035 m
Detection range	Radius: 3500 mm
Mounting height	2.5 m

### Environment

IP degree of protection	IP20
-------------------------	------

### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.