

# 5000ETP10W

## Ethernet Touch Panel, C-Bus Control and Management System, Price On Application



### Main

Range	C-Bus
Product or component type	Touch panel
Device application	Equipment monitoring and control
Display colour	262000 colours
Display size	10.1 inch
Provided equipment	1 mounting plate 1 cover frame 10 fixing screws 4 washer 1 screw 1 desk stand 1 micro SD card securing plate 1 Ethernet cable securing plate
Cover frame colour tint	White

### Complementary

Supply	External power supply: 12 V DC, +/- 5 %, <1.5 A Via PoE: - 15 W
Maximum power consumption in W	6 W typical
Standby consumption	< 0.5 W
Display resolution	1280 x 800 pixels
Brightness	300 cd/m <sup>2</sup>
View angle horiz x vert	170° horizontal 170° vertical
Communication port protocol	Ethernet
Port Ethernet	10/100BASE
Integrated connection type	Ethernet port USB port HDMI Micro SD card port Audio output
Connector type	Power input
Contrast ratio	800:1
Aspect ratio	16:9
Response time	30 ms typical
Mounting location	Wall mounting
Device mounting	Flush Surface
Width	Cover frame: 316 mm
Height	Cover frame: 220 mm
Depth	Cover frame: 6 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	10...85 %
Standards	IEEE 802.3af

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	23.0 cm
Package 1 Length	35.0 cm
Package 1 Weight	1.55 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Height	38.0 cm
Package 2 Width	24.5 cm
Package 2 Length	43.5 cm
Package 2 Weight	6.2 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins