

Product data sheet

Characteristics

5041NMS

Push button interface, C-Bus, 40 Series auxiliary module



Main

Range	C-Bus
Product brand	Clipsal
Product name	Series 40M
Product or component type	Push-button interface
Device application	Control
Module type	Auxiliary
Colour	Transparent green
Switch application	Load switching Dimming up/down control Timer Scene control Bell switch Shutter control Fan speed control Blind control

Complementary

Range compatibility	C-Bus Iconic wall plate Pro Series wall plate
Dimmer control	255 possible levels
Device mounting	Wall mounted by Series 40M grid
Input impedance	100 kOhm at 1 kHz
Local signalling	LED (red/blue) for status
Suitable cable type	Twisted unshielded pairs cable category 5e
Isolation voltage	3.75 kV from C-Bus to mains
Communication network type	C-Bus via 40 series main module
Control type	Push-button
Depth	14.5 mm
Width	22.8 mm
Height	22.8 mm
Net weight	0.007 kg
Material	Plastic
Starting time	5 s
Module configuration	Programmed with learn mode Programmed with C-Bus software
Time delay range	1s...18h12m15s
Current consumption	18 mA

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	15 g
Package 1 Height	27 mm
Package 1 width	27 mm
Package 1 Length	25 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information