

Product data sheet

Characteristics

755PFM

SMOKE ALARM PHOTO FLUSH



Main

Range	Fire Tek
Product brand	Clipsal
Product or component type	Smoke detector
Device application	Early detection of smouldering fires and open fires
Electronic sensor type	Photo-electric sensor

Complementary

Supply	Mains
[Us] rated supply voltage	220...240 V AC 50 Hz
[Ue] rated operational voltage	9/230 V
Detection type	Heat
Function available	Local alarm
Control type	Button (test/hush function)
Horn level	85 dB at 3 m, minimum
Time delay range	10 min (hush)
Material	Thermoplastic
Type of installation	Indoor
Device mounting	Surface
Mounting support	Ceiling
Fixing mode	By screws


Environment

IP degree of protection	IP20
Ambient air temperature for operation	0...45 °C
Ambient air temperature for storage	-20...60 °C
Relative humidity	5...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11 cm
Package 1 Width	15 cm
Package 1 Length	15 cm
Package 1 Weight	402 g

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--