

## Product data sheet

### Characteristics

# A9Z51240

## Acti9 iID - Residual Current Circuit Breaker - 2P - 40A - 30mA - B type



### Main

Range	Acti9
Product name	Acti9 iID
Product or component type	Residual current circuit breaker (RCCB)
Device short name	iID
Device application	Electrical Vehicle charger
Poles description	2P
Neutral position	Left
[In] rated current	40 A
Network type	AC
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type B-EV (Electric Vehicle)
Quality labels	VDE NF IMQ KEMA

### Complementary

Device location in system	Outgoer Group incomer
Network frequency	50 Hz
[Ue] rated operational voltage	230 V AC 50 Hz
Residual current tripping technology	Voltage independent
Rated breaking and making capacity	I <sub>dm</sub> 1500 A I <sub>m</sub> 1500 A
Rated conditional short-circuit current	10 kA
[Ui] rated insulation voltage	250 V
[Uimp] rated impulse withstand voltage	6 kV
Contact position indicator	Yes
Control type	Toggle
Local signalling	Trip indicator ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	88 mm
Width	72 mm
Depth	79 mm
Net weight	350 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	15000 cycles
Locking options description	Padlocking device

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Connections - terminals	Double terminal front 1...35 mm <sup>2</sup> rigid Double terminal front 1...25 mm <sup>2</sup> flexible Double terminal front 1...25 mm <sup>2</sup> flexible with ferrule Double terminal back 1...25 mm <sup>2</sup> rigid Double terminal back 1...16 mm <sup>2</sup> flexible Double terminal back 1...16 mm <sup>2</sup> flexible with ferrule
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom

## Environment

Standards	IEC 61008-2-1 IEC/EN 62423 EN 61008-2-1
Product certifications	CCC[RETURN]KC
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
IK degree of protection	IK05
Pollution degree	3
Overvoltage category	IV
Electromagnetic compatibility	8/20 μs impulse withstand, 3 kA conforming to EN/IEC 61008-1
Operating altitude	0...2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	8.5 cm
Package 1 Length	10.0 cm
Package 1 Weight	361.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	10.227 kg

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins