

Product data sheet

Characteristics

EVP1CNX32121

EVlink Charging cable 10m 32A 1-Phase T2-T1 IEC EV accessory



Main

Range	EVlink
Product or component type	Charging cable
Accessory / separate part category	Cabling accessory
Network number of phases	Single phase
Poles description	1P + N
[In] rated current	32 A
[Us] rated supply voltage	220...240 V AC 50/60 Hz
Socket number	2

Complementary

Plug type	T1 / silver plated contacts charging station end
Connector type	T2 charging station end silver plated contacts T1 vehicle end silver plated contacts
Range compatibility	EVlink parking EVF1 charging station EVlink parking EVW1 charging station EVlink parking EVF2 charging station EVlink parking EVW2 charging station EVlink Smart Wallbox EVB1 charging station EVlink Wallbox EVH2 charging station
Standards	IEC 62196-1 IEC 62196-2
Product certifications	CE
Length	10 m
Net weight	4.1 kg
Colour	Grey

Environment

IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	5...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3.798 kg
Package 1 Height	7 cm
Package 1 width	38 cm
Package 1 Length	42 cm
Unit Type of Package 2	S04
Number of Units in Package 2	2
Package 2 Weight	8.45 kg

Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm
Unit Type of Package 3	P06
Number of Units in Package 3	8
Package 3 Weight	40.95 kg
Package 3 Height	75 cm
Package 3 width	60 cm
Package 3 Length	80 cm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration