

Product data sheet

Characteristics

PDL395USBC-VW

Twin socket with USB Type C, PDL Iconic, Fast charger, 25W, 10A, 220-240V, AC, vivid white

Main

Range of product	Iconic
Range	PDL Iconic
Product or component type	Switched socket with USB charger
Device presentation	Complete product
Product brand	PDL
Outlet poles configuration	2P + E with shutter
Outlet standard	Australian
Switch application	Control

Complementary

Device mounting	Flush
Mounting position	Horizontal
Number of power socket outlets	2
Number of rocker	2
Range compatibility	Iconic switched socket with USB charger
Outlet standard description	With earthing contact
Outlet standard deviation	Australian/New Zealand
Ground lug position	Straight 180° position
Pin number	3
Fixing mode	By screw
Installation direction	Horizontal
Surface finish	Matt
Type of packing	Polybag
Quantity per set	1 set of 10
Sale per indivisible quantity	1
Rated current	10 A at 220...240 V AC 50 Hz
Connections - terminals	3 screw terminals
Screwdriver shape	Square drive no 1 (SQ1)
Clamping connection capacity	1 x 2.5...4 x 2.5 mm ² for stranded cable(s)
Wire stripping length	16 mm
Material	PC (polycarbonate): cover frame ABS (acrylonitrile butadiene-styrene): cover frame PC (polycarbonate): fixing frame
Height	120 mm
Width	78 mm
Depth	55 mm

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZS 3112

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	2.7 cm
Package 1 Length	4.7 cm
Package 1 Weight	105.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	21.8 cm
Package 2 Width	10.2 cm
Package 2 Length	14.65 cm
Package 2 Weight	552 g

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	7