



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or component type	Uninterruptible power supply (UPS)
Cable length	1.52 m
Battery type	Lead-acid battery Sealed rechargeable Internal battery
Range of product	Easy UPS 1Ph BVS Series

Complementary

Display type	LED indicator
Type of signal	Sine wave
Transfer time	6 ms typical : 10 ms maximum
Network frequency	50...60 Hz
Power range	500 VA
Electrical connection	Output: 4 outlet Australian Input: 1 cable
Local signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LCD display for status and alert
Charging time	8 h
Net weight	3.9 kg
Height	9.25 cm
Width	16.05 cm
Depth	30.5 cm

Environment

Relative humidity	0...90 %, non-condensing
Operating altitude	0...1968.3 m
Ambient air temperature for operation	0...40 °C
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Product certifications	CE[RETURN]RCM

Physical

Mounting support	Wall-mount
------------------	------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.362 cm
Package 1 Width	1.422 cm
Package 1 Length	3.734 cm
Package 1 Weight	4.2 kg
SCC14	10731304346453

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years
----------	---------