



Main

Range	Acti9
Device short name	MSC 18
Product or component type	Chassis
Device application	Distribution

Complementary

Range compatibility	Acti9 Acti9 Isobar B distribution board
[In] rated current	250 A
Rated voltage	415 V AC 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Icw] rated short-time withstand current	25 kA
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of ways	1 way (incomer) - 3P 36 ways (outgoer)
Outgoer Pole capacity	36 x 18 mm
Length	326 mm
Width	215 mm

Environment

Standards	AS/NZS 61439
-----------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations