

## Product data sheet

### Characteristics

# PDL680M32WH

Switch 600 Series Mechanism - Single-pole - 1-gang - Marked OFF-AIRCON - 250 V - 32 A / 20 AX - White



#### Main

|                           |            |
|---------------------------|------------|
| Range of product          | 600 Series |
| Product or component type | Switch     |
| Control type              | Rocker     |

#### Complementary

|                                       |                       |
|---------------------------------------|-----------------------|
| Material                              | PA (polyamide)        |
| Colour tint                           | White                 |
| Surface finish                        | Gloss                 |
| Installation direction                | Vertical              |
| Length                                | 23 mm                 |
| Width                                 | 23 mm                 |
| Rated current                         | 20 AX<br>32 A         |
| [Ue] rated operational voltage        | 250 V                 |
| Network type                          | AC                    |
| Motor M-rating AS3133                 | M180                  |
| Network number of phases              | 1 phase               |
| Number of gangs                       | 1 gang                |
| Number of poles                       | 1                     |
| Mounting mode                         | Front                 |
| Ambient air temperature for operation | -10...40 °C           |
| Cable cross section                   | 2 x 6 mm <sup>2</sup> |

#### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 3.5 cm   |
| Package 1 Width              | 2.5 cm   |
| Package 1 Length             | 2.5 cm   |
| Package 1 Weight             | 19.385 g |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| EU RoHS Directive          | Compliant with Exemptions                     |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations      |