

Product data sheet

Characteristics

PDL925RWH

Back Entry Heavy Duty Cord Connector; 10A, White



Main

Range of product	900 Series
Product or component type	Socket
Material	PC (polycarbonate)
Colour tint	White

Complementary

Surface finish	Gloss
Width	45 mm
Diameter	45 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Network number of phases	1 phase
Pin number	3
Ambient air temperature for operation	-10...40 °C
Cable cross section	0.75...1.5 mm ²
Connector type	Screw terminals
Quantity per set	Set of 20
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	5 cm
Package 1 Length	5.5 cm
Package 1 Weight	0.043 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	12 cm
Package 2 Width	15.3 cm
Package 2 Length	19.4 cm
Package 2 Weight	1.08 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	21.6 cm

Package 3 Width	32.5 cm
Package 3 Length	62.9 cm
Package 3 Weight	11300.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations