


Product data sheet

Characteristics

VDIB1778XUTN

Actassi S-110 Connector RJ45 40 Mech

Unshielded Cat6A ICONIC - 40 Mech - pk x 1



Main

Range	Actassi
Product type	RJ45 network socket
Device presentation	Integrated shutter Two piece design
Colour tint	Stuffer cap: transparent (ABS + PC) IDC cover: blue (ABS + PC) Connector housing: translucent (ABS + PC)
Wiring Colour configuration	568 A/B
Quantity per set	Set of 1

Complementary

[In] rated current	1.5 A at 25 °C
Voltage proof	1000 V AC/DC peak, between contacts
Insulation resistance	Initial insulation resistance: ≥ 500 MOhm at 100 V DC
AWG gauge	AWG 23...AWG 24
Durability	750 cycles
Coupling attenuation	≥ 35 dB at 30...100 MHz $\geq 75 - 20 \times \log(f)$ dB at 100...1000 MHz
Contact pins	8 pins of copper alloy and gold plated conforming to IEC 60603-7
Pulling force	50 N during 60 s
Transverse conversion loss	≥ 50 dB $\geq 68 - 20 \times \log(f)$ dB at 1...500000 kHz
Tool type	Punch down tool Quick termination tool
Cable outer diameter	0.9...1.1 mm
Compatible LAN cable types	UTP
Communication network category	6A
Supported applications	10GBASE-T
Protocols	VoIP (Voice IP) PoE+ (Power over Ethernet)
Product compatibility	RJ45 plug
Transmission frequency	0...500 MHz
Type of footprint	S-110 40 mech
Height	22 mm
Length	36 mm
Width	16 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Operational temperature range	-40...70 °C
Climatic category	40/070/21 (21 days)
Flame retardance	UL94-V0 conforming to UL listed
Product certifications	RCM
Standards	AS/NZS 3080 AS/CA S008 ISO/IEC 11801 IEC 60603-7-41 ANSI/TIA-568-C.2.1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	2.3 cm
Package 1 Length	1 cm
Package 1 Weight	10 g

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--