

Product data sheet

Characteristics

5031NMMIRL

C-BUS 30 SER MECH MASTER IR



Main

Range of product	Series 30M
Product brand	Clipsal
Product or component type	IR capable master mechanism

Complementary

Range compatibility	C-Bus
Device mounting	Wall mounted by Series 30M grid
[Ue] rated operational voltage	15...36 V DC
Input impedance	100 kOhm at 1 kHz
Local signalling	LED (blue/orange) for status
Suitable cable type	Twisted unshielded pairs cable category 5e
Isolation voltage	3.75 kV from C-Bus to mains
Communication network type	C-Bus

Environment

Relative humidity	10...95 % non-condensing
-------------------	--------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	54 g
Package 1 Height	2.8 cm
Package 1 width	6.4 cm
Package 1 Length	10 cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Circularity Profile	End Of Life Information

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.