



Main

Product or component type	Control unit
Trip unit name	MicroLogic 2.0 A
Trip unit technology	Electronic
Range compatibility	MasterPact NT MasterPact NW Compact NS Masterpact MT
Device application	Distribution
Number of poles	4P 3P
Protected poles description	4t 3t 3t + N/2
Trip unit protection functions	Basic protection
Protection type	For overload protection (long time) For instantaneous short-circuit protection
Trip unit rating	630 A at 50 °C 800 A at 50 °C 1000 A at 50 °C 1250 A at 50 °C 1600 A at 50 °C 2000 A at 50 °C 2500 A at 50 °C 3200 A at 50 °C 4000 A at 50 °C 5000 A at 50 °C 6300 A at 50 °C
Network type	AC
Network frequency	50/60 Hz
Circuit breaker mounting mode	Fixed Drawout

Complementary

Long-time pick-up adjustment type Ir (thermal protection)	Adjustable 9 settings
[Ir] long-time protection pick-up adjustment range	0.4...1 x In
Long-time protection delay adjustment type tr	Adjustable 9 settings
[tr] long-time protection delay adjustment range	0.7...16.6 S at 7.2 x Ir 0.7...24 S at 6 x Ir 12.5...600 s at 1.5 x Ir
Thermal memory	20 mn
Instantaneous protection pick-up adjustment type li	Adjustable 9 settings
[li] instantaneous protection pick-up adjustment range	1.5...10 x Ir
Earth-leakage protection	Without
Zone selective interlocking ZSI	Without
Local signalling	3 LEDs (red) for electrical fault 1 LED (red) for internal error
Display type	Digital display
Type of measurement	Ammeter
Communication of data	Measurement readout Protection and alarm settings

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------