

Product data sheet

Characteristics

753R-WE

Motion Sensor Infrascan - Passive infrared -
Indoor - 5m detection radius - 3-wire - 240 V -
10 A - White Electric



Main

Range	Infrascan
Product brand	Clipsal
Product or component type	Movement sensor
Device application	Lighting
Sensor type	PIR
Product specific application	Staircase monitoring
Colour	White electric

Complementary

[Ue] rated operational voltage	200...265 V AC
Network frequency	50 Hz
Inrush current	10 A
Power range	<= 230 W
Protection type	Creep zone protection
Function available	Automatic with manual override
Movement detection area	14 m
Horizontal detection angle	0...360 °
Time delay range	0...5 s (switch-on)
Duty cycle	20 min
Detection face	Lateral: 7 m Frontal: 7 m
Material	Plastic
Surface finish	Brilliant
Device mounting	Flush
Mounting support	Ceiling
Mounting height	2.4 m
Colour code	WE

Environment

IP degree of protection	IP20
Ambient air temperature for operation	0...50 °C

Packing Units

Package 1 Weight	204.000 g
Package 1 Height	165.000 mm
Package 1 width	85.000 mm
Package 1 Length	125.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information