



Main

Device application	Distribution
Range of product	Acti9
Range	Acti9
Product name	XC60
Product or component type	Miniature circuit-breaker
Device short name	xC60
Poles description	4P
Number of protected poles	4
[In] rated current	63 A
Network type	AC DC
Trip unit technology	Thermal-magnetic
Curve code	C
Utilisation category	Category A conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to EN/IEC 60947-2

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	240 V AC 50/60 Hz 380...415 V AC 50/60 Hz 220...250 V DC
Magnetic tripping limit	8 x In +/- 20 %
Breaking capacity	10000 A Icn at 240 V AC 50/60 Hz conforming to EN/IEC 60898-1 10000 A Icn at 415 V AC 50/60 Hz conforming to EN/IEC 60898-1 10 KA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 6 kA Icu at 220...250 V DC conforming to EN/IEC 60947-2
[Ics] rated service breaking capacity	7.5 KA conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 6 kA conforming to EN/IEC 60947-2 - 220...250 V DC
Limitation class	3 conforming to EN/IEC 60898-1 3 conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	35 mm DIN rail
Comb busbar and distribution block compatibility	Top: YES
9 mm pitches	8
Height	85 mm
Width	72 mm
Depth	77.5 mm
Net weight	0.415 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Connections - terminals	Biconnect (top) Tunnel type terminals (bottom) 25 mm ² flexible Tunnel type terminals (bottom) 35 mm ² rigid
Wire stripping length	13 mm for top or bottom connection
Tightening torque	3.5 N.m
Earth-leakage protection	Separate block
Product compatibility	C60 auxiliary C60 accessories
Overvoltage category	IV

Environment

Standards	EN/IEC 60898-1 EN/IEC 60947-2
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-30...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.8 cm
Package 1 Width	9 cm
Package 1 Length	8.2 cm
Package 1 Weight	480 g
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	8.6 cm
Package 2 Width	9.4 cm
Package 2 Length	24 cm
Package 2 Weight	1.54 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	36
Package 3 Height	27.2 cm
Package 3 Width	30 cm
Package 3 Length	36 cm
Package 3 Weight	19.06 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Sustainable packaging	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts & cables product