

Product data sheet

Characteristics

A9FDB610

Acti9 - iDPN N Arc - 1P+N 10A C 6000A - Arc fault detection circuit breaker



Main

Range	Acti9
Product name	Acti9 iDPN N Arc
Product or component type	Arc fault detection circuit breaker
Product specific application	Fire prevention by arc detection
Standards	IEC 60898-1 EN/IEC 62606
Device short name	iDPN N Arc
Poles description	1P + N
[In] rated current	10 A at 30 °C
Curve code	C
Breaking capacity	6000 A Icn at 230 V AC 50 Hz conforming to EN/IEC 60898-1
Network type	AC
Neutral position	Left
Trip unit technology	Thermal-magnetic

Complementary

Number of protected poles	1
Network frequency	50 Hz
[Ue] rated operational voltage	230 V AC 50 Hz conforming to IEC 62606 230 V AC 50 Hz conforming to EN/IEC 60898-1
Device location in system	Outgoer
Magnetic tripping limit	5...10 x In
Limitation class	3 conforming to IEC 60898-1
Threshold tripping voltage	400 V 200 ms
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60898-1
[Ui] rated insulation voltage	400 V AC
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON, OFF, fault trip
Mounting mode	Clip-on
Mounting support	DIN rail
Colour	White
Mechanical durability	20000 cycles
Electrical durability	20000 cycles 230 V AC 50 Hz
Overvoltage category	III
Cable entry	Top
Connections - terminals	Tunnel type terminal for 1 cable(s) 10 mm ² flexible Tunnel type terminal for 2 cable(s) 2.5 mm ² flexible Tunnel type terminal for 1 cable(s) 16 mm ² rigid Tunnel type terminal for 2 cable(s) 2.5 mm ² rigid
Wire stripping length	14 mm
Tightening torque	2 N.m

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Comb busbar and distribution block compatibility	ProDis Librio
Connection pitch	9 mm between phase and neutral
9 mm pitches	4
Height	81 mm
Width	36 mm
Depth	72 mm
Net weight	190 g

Environment

Heat dissipation	2.6 W at 230 V - 10 A
IP degree of protection	IP20
Pollution degree	2
Tropicalisation	Severity B conforming to IEC 60068-2-30 for 28 d
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C
Product certifications	RCM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	8.500 cm
Package 1 Length	10.000 cm
Package 1 Weight	221.300 g
Unit Type of Package 2	S02
Number of Units in Package 2	8
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.020 kg
Unit Type of Package 3	P12
Number of Units in Package 3	128
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	44.866 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins