

Product data sheet

Characteristics

EVH2S22P04K

EVlink Wallbox - 22 kW - T2 socket outlet with shutter - charging station



Main

| | |
|---------------------------|-------------------------------|
| Range | EVlink |
| Product name | EVlink Wallbox |
| Product or component type | Charging station |
| Device short name | EVH2 |
| Poles description | 3P + N |
| Mounting mode | Wall-mounted |
| Offer type | Standard |
| Max power | 22 kW 32 A |
| Number of charge point | 1 |
| Connection to the vehicle | Socket-outlet T2 with shutter |
| Access control system | Key |

Complementary

| | |
|------------------------|---|
| Rated supply voltage | 380...415 V AC 50/60 Hz |
| Earthing system | TT TN |
| Number of inputs | 1 |
| Input type | Contact for power limitation Contact for delayed charging |
| Control type | 1 white button, function: stop/restart Green button, function: cable unlocking |
| Local signalling | 1 multi-colour LED, function: status indication |
| Height | 480 mm |
| Width | 331.5 mm |
| Depth | 170 mm |
| Net weight | 5.6 kg |
| Colour | White (RAL 9003) Grey (RAL 7016) |
| Standards | IEC 62196-2 IEC 62196-1 IEC 61851-1 IEC 61851-22 |
| Product certifications | CB[RETURN]CE |

Environment

| | |
|---------------------------------------|------------------------------|
| IP degree of protection | IP54 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |
| Ambient air temperature for operation | -30...50 °C |
| Ambient air temperature for storage | -40...80 °C |
| Relative humidity | 5...95 % |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 26.000 cm |
| Package 1 Width | 40.000 cm |
| Package 1 Length | 53.500 cm |
| Package 1 Weight | 8.120 kg |
| Unit Type of Package 2 | P06 |
| Number of Units in Package 2 | 4 |
| Package 2 Height | 50.000 cm |
| Package 2 Width | 60.000 cm |
| Package 2 Length | 80.000 cm |
| Package 2 Weight | 41.940 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile |  End Of Life Information |