

## Product data sheet

### Characteristics

# EVH2S22P0CK

EVlink Wallbox - 22 kW - T2 attached cable - charging station



### Main

Range	EVlink
Product name	EVlink Wallbox
Product or component type	Charging station
Device short name	EVH2
Poles description	3P + N
Mounting mode	Wall-mounted
Offer type	Standard
Max power	22 kW 32 A
Number of charge point	1
Connection to the vehicle	Attached cable T2 4 m
Access control system	Key

### Complementary

Rated supply voltage	380...415 V AC 50/60 Hz
Earthing system	TT TN
Number of inputs	1
Input type	Contact for power limitation Contact for delayed charging
Control type	1 white button, function: stop/restart Green button, function: cable unlocking
Local signalling	1 multi-colour LED, function: status indication
Height	480 mm
Width	330 mm
Depth	170 mm
Net weight	7.5 kg
Colour	White (RAL 9003) Grey (RAL 7016)
Standards	IEC 62196-1 IEC 62196-2 IEC 61851-22 IEC 61851-1
Product certifications	CB CE

### Environment

IP degree of protection	IP54 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	5...95 %

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	10.3 kg
Package 1 Height	27.2 cm
Package 1 width	40 cm
Package 1 Length	53.2 cm
Unit Type of Package 2	P06
Number of Units in Package 2	4
Package 2 Weight	50.356 kg
Package 2 Height	50 cm
Package 2 width	60 cm
Package 2 Length	80 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>