



Main

Range	EasyPact
Product name	EasyPact TVS
Product or component type	Control relay
Device short name	CAE
Contactor application	Control circuit
Colour	Grey (RAL 7011)

Complementary

Utilisation category	AC-15 AC-14
Pole contact composition	2 NO + 2 NC
[Ue] rated operational voltage	<= 690 V AC
Control circuit type	AC at 50 Hz
[Uc] control circuit voltage	110 V AC 50 Hz
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
[Ith] conventional free air thermal current	10 A (at 40 °C)
Irms rated making capacity	140 A at 690 V AC conforming to IEC 60947-5-1
[Icw] rated short-time withstand current	120 A - 500 ms 140 A - 100 ms
Associated fuse rating	10 A gG at 690 V conforming to IEC 60947-5-1
[Ui] rated insulation voltage	690 V conforming to IEC 60947-5-1
Mounting support	Plate Rail
Connections - terminals	Screw clamp terminals 1 1...2.5 mm ² - cable stiffness: flexible without cable end Screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible without cable end Screw clamp terminals 1 1...2.5 mm ² - cable stiffness: flexible with cable end Screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible with cable end Screw clamp terminals 1 1...2.5 mm ² - cable stiffness: solid without cable end Screw clamp terminals 2 1...2.5 mm ² - cable stiffness: solid without cable end
Recommended tightening torque	1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2
Control circuit voltage limits	Operational: 0.85...1.1 Uc at 50 Hz Drop-out: 0.3...0.6 Uc
Operating time	4...19 ms coil energisation and NC opening 12...22 ms coil energisation and NO closing 4...12 ms coil de-energisation and NC opening 6...17 ms coil de-energisation and NO closing
Mechanical durability	10 Mcycles
Maximum operating rate	180 cyc/mn
Inrush power in VA	70 VA 50 Hz (at 20 °C)
Hold-in power consumption in VA	8 VA 50 Hz (at 20 °C)
Minimum switching voltage	17 V
Minimum switching current	5 mA
Non-overlap time	1.5 Ms on energisation between NC and NO contact 1.5 ms on de-energisation between NC and NO contact
Insulation resistance	> 10 MOhm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mechanical robustness	Shocks control relay open: 7 Gn for 11 ms Shocks control relay closed: 10 Gn for 11 ms Vibrations control relay open: 1.5 Gn, 5...300 Hz Vibrations control relay closed: 3 Gn, 5...300 Hz
Height	74 mm
Width	45 mm
Depth	80 mm
Net weight	0.28 kg






Environment

Standards	IEC 60947-5-1
Product certifications	GOST
IP degree of protection	IP2x conforming to IEC 60529
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-20...70 °C
Ambient air temperature for storage	-60...80 °C
Operating altitude	3000 m without derating

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	305 g
Package 1 Height	5.2 cm
Package 1 width	7.5 cm
Package 1 Length	8.7 cm
Unit Type of Package 2	S02
Number of Units in Package 2	36
Package 2 Weight	10.08 kg
Package 2 Height	15 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P06
Number of Units in Package 3	576
Package 3 Weight	179.32 kg
Package 3 Height	115 cm
Package 3 width	60 cm
Package 3 Length	80 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------