

Product data sheet

Characteristics

EVP1CNL32121

EVlink Charging cable 7m 32A 1-Phase T2-T1
IEC EV accessory



Main

Range	EVlink
Product or component type	Charging cable
Accessory / separate part category	Cabling accessory
Network number of phases	Single phase
Poles description	1P + N
[In] rated current	32 A
[Us] rated supply voltage	220...240 V AC 50/60 Hz
Socket number	2

Complementary

Plug type	T1 / silver plated contacts charging station end
Connector type	T2 charging station end silver plated contacts T1 vehicle end silver plated contacts
Range compatibility	EVlink EVlink parking EVF1 charging station EVlink EVlink parking EVW1 charging station EVlink EVlink parking EVF2 charging station EVlink EVlink parking EVW2 charging station EVlink EVlink Smart Wallbox EVB1 charging station EVlink EVlink Wallbox EVH2 charging station
Standards	IEC 62196-1 IEC 62196-2
Product certifications	CE
Length	7 m
Net weight	3 kg
Colour	Grey

Environment



IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	5...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	34.000 cm
Package 1 Length	38.000 cm
Package 1 Weight	3.003 kg
Unit Type of Package 2	S04
Number of Units in Package 2	3
Package 2 Height	30.000 cm

Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	9.897 kg
Unit Type of Package 3	P06
Number of Units in Package 3	12
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	39.588 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes