

Product data sheet

Characteristics

EVP1CNS32322

Charging cable, EVlink, 5m, 32A, 3-Phase, T2 connector at each end of cable



Main

Range	EVlink
Product or component type	Charging cable
Accessory / separate part category	Cabling accessory
Network number of phases	Three phase
Poles description	3P + N
[In] rated current	32 A
[Us] rated supply voltage	380...415 V AC 50/60 Hz
Socket number	2

Complementary

Plug type	T2 / silver plated contacts charging station end
Connector type	T2 vehicle end silver plated contacts T2 charging station end silver plated contacts
Range compatibility	EVlink EVlink parking EVF1 charging station EVlink EVlink parking EVW1 charging station EVlink EVlink parking EVF2 charging station EVlink EVlink parking EVW2 charging station EVlink EVlink Smart Wallbox EVB1 charging station EVlink EVlink Wallbox EVH2 charging station EVlink EVlink Pro AC EVB3 charging station EVlink EVlink Pro AC Metal EVB3 charging station
Standards	IEC 62196-2 IEC 62196-1
Product certifications	CE
Length	5 m
Net weight	3.2 kg
Colour	Grey

Environment

IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	5...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.000 cm
Package 1 Width	38.000 cm
Package 1 Length	40.000 cm
Package 1 Weight	3.293 kg

Unit Type of Package 2	S06
Number of Units in Package 2	25
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	95.875 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information