

## Product data sheet

### Characteristics

# ML2015/15I-WE

Medilec, Single Switch Socket Outlet, 250V, 15A, Circuit Identification



### Main

|                           |                                  |
|---------------------------|----------------------------------|
| Range of product          | ML2000 Moulded Series<br>Medilec |
| Product or component type | Switched socket                  |
| Product brand             | Clipsal                          |

### Complementary

|                                |                         |
|--------------------------------|-------------------------|
| Control type                   | ON/OFF button           |
| Number of gangs                | 1 gang                  |
| Pin number                     | 3                       |
| Number Of Outlets              | 1                       |
| Actuator                       | Rocker<br>Switch        |
| Mounting Type                  | By screws               |
| Local signalling               | Without light indicator |
| Installation Orientation       | Horizontal              |
| Material                       | Plastic                 |
| [Ue] rated operational voltage | 250 V AC                |
| [In] rated current             | 15 A                    |
| Length                         | 116 mm                  |
| Width                          | 76 mm                   |

### Environment

|           |             |
|-----------|-------------|
| Standards | AS/NZS 3112 |
|-----------|-------------|

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 3.4 cm  |
| Package 1 Width              | 8 cm    |
| Package 1 Length             | 12.8 cm |
| Package 1 Weight             | 96 g    |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |  |
|----------------------------|--|
| REACH Regulation           | <a href="#">REACH Declaration</a>      |
| EU RoHS Directive          | Compliant with Exemptions              |
| Mercury free               | Yes                                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a> |
| RoHS exemption information | <a href="#">Yes</a>                    |